

Table 4-1 Main Adjustment Parameter (Zilog μ -com) NON TTX

FUNCTION	OSD ABBREVIATION	RANGE	INITIAL DATA
AUTO GAIN CONTROL	AGC	0 ~ 63 STEP	40
SUB BRIGHT	SBT	0 ~ 63 STEP	44
SUB CONTRAST	SCT	0 ~ 63 STEP	32
SUB COLOR	SCR	0 ~ 27 STEP	13
SUB TINT	STT	0 ~ 27 STEP	13
PAL DELAY	PDL	0 ~ 7 STEP	2
NTSC DELAY	NDL	0 ~ 7 STEP	2
RED CUTOFF	RC	0 ~ 254 STEP	0
GREEN CUTOFF	GC	0 ~ 254 STEP	0
BLUE CUTOFF	BC	0 ~ 254 STEP	0
RED-GREEN DRIVE GAIN	RG	0 ~ 63 STEP	32
BLUE-GREEN DRIVE GAIN	BG	0 ~ 63 STEP	32
PAL VERTICAL SLOPE	PSL	0 ~ 31 STEP	15
PAL VERTICAL SHIFT	PVS	0 ~ 15 STEP	6
PAL VERTICAL AMPLITUDE	PVA	0 ~ 63 STEP	32
PAL HORIZONTAL SHIFT	PHS	0 ~ 15 STEP	0
NTSC VERTICAL SLOPE	NSL	0 ~ 31 STEP	15
NTSC VERTICAL SHIFT	NVS	0 ~ 15 STEP	6
NTSC VERTICAL AMPLITUDE	NVA	0 ~ 63 STEP	32
NTSC HORIZONTAL SHIFT	NHS	0 ~ 15 STEP	0

NOTE : PVS,PVA, PHS, NVS, NVA,NHS parameters must be aligned using both the 50Hz and 60Hz vertical-field rates.